

Clamp for Strut Insert Pistons - 60mm Bolts

Designed to lock a MacPherson Strut in its fully extended position when changing the springs.



Additional Information

- Particularly useful when working with struts that are equipped with strong internal springs (tension stop springs) that pull the strut shaft
 partly into the strut.
- · For strut pistons with max. diameter of 36mm.
- · Kit includes 60mm long bolts (68mm including head).
- Included in Laser MacPherson Strut Expander Tool Set, Part No. 5790.

http://lasertools.co.uk/product/6270



| Distributed by The Tool Connection Ltd. | Cineton Road | Southam | Warwickshire | CV47 0DR | +44 (0) 1926 815 888 | | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 888 | CV47 0DR | +44 (0) 1926 815 818 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 815 | +44 (0) 1926 | +44 (0) 1926 | +44 (0) 1926 | +44 (0) 1926 | +44 (0) 1926 |

LASER Kamasa Gunson Connect







